


Fluke BP290 2400 mAh High Capacity Li-Ion Battery for Fluke 190-Series-II



Wichtigste Merkmale

- 2400 mAh rechargeable Li-ion battery
- Compatible with ScopeMeter® 190 Series III, 190 Series II, 120B Series, MDA-500 Series Motor Drive Analyzers and 430-II Series Power Quality Analyzers

Produktübersicht: Fluke BP290 2400 mAh High Capacity Li-Ion Battery for Fluke 190-Series-II

The Fluke BP290 Li-ion Battery is a standard capacity battery for use in Fluke 190 Series II and Series III ScopeMeter Test Tools, 120B Series ScopeMeter Test Tools, MDA-500 Series III Motor Drive Analyzers and 430-II Series Power Quality Analyzers. BP290 Li-ion batteries include a charge-status indicator so you can quickly and easily verify charge status in the field, and may be charged either in the instrument itself, or using the option [EBC290 External Charger](#). For situations requiring longer battery operating time consider the [Fluke BP291 4800 mAh High Capacity Li-Ion Battery](#).

Technische Daten: Fluke BP290 2400 mAh High Capacity Li-Ion Battery for Fluke 190-Series-II

Baery	Li-ion, 10.8 V, 2500 mAh, 27 Wh configuration 3ICR19/66
Safety	Pollution degree 2
Operating temperature	0 °C to +50 °C (charging may slow or stop at environmental temperatures >40 °C)
Storage temperature	-20 °C to +60 °C
Recommended storage temperature	<35 °C
Humidity	0 °C to 10 °C noncondensing 10 °C to 30 °C @ 95 % (±5 %) rh 30 °C to 40 °C @ 75 % (±5 %) rh
Altitude	3000 m
Weight	175 g
Dimensions	22 mm x 85 mm x 59 mm

Modelle



Fluke BP290

2400 mAh High Capacity Li-Ion Battery for Fluke 190-series II

Fluke. *Damit Ihre Welt intakt bleibt.*

Fluke Deutschland GmbH

In den Engematten 14

79286 Glottertal

Telefon: 0 69 2 2222 0203

E-Mail: CS.Deutschland-ELEK@Fluke.com

E-Mail: CS.Deutschland-INDS@Fluke.com

www.fluke.de

©2025 Fluke Corporation. Alle Rechte vorbehalten.

Anderungen vorbehalten

03/2025

Technischer Beratung:

Beratung zu Produkteigenschaften, Spezifikationen,

Messgeräte und Anwendungsfragen

Tel.: +49 (0) 7684 8 00 95 45

E-Mail: techsupport.dach@fluke.com

**Dieses Dokument darf nicht ohne die schriftliche
Genehmigung der Fluke Corporation geändert
werden.**